


Product Details


Mirror TV

MaJico

Cosmetic Mirror TV CUBIK 6.4



- New LCD activ matrix, integrated in mirror surface
- Integrated TV monitor:
 - Size: 129 x 96 mm / diagonal 163 mm (6,4")
 - Video signals: PAL / NTSC
 - Power supply: DC 12 V (rating)
 - Power: 10 W / 830 mA (typical)
- TV when switched ON
- Mirror when switched OFF
- Twin arm with full pivotal adjustment
- Material: brass
- Class I, 220-250 V



- ▶ To be connected to an existing TV system (slave installation):

Code	Version	Mirror
without loud speaker		
020621	chrome	215 x 215 mm
with integrated loud speaker		
020629	chrome	215 x 215 mm

Cleaning Instructions - Magnifying Mirrors:

- **Mirror Lens**
Wipe down with a light solution of soap suds. Do NOT use sponges or cloths that may damage the surface. Wipe with a damp cloth. Polish with a dry soft cotton cloth.
- **Chrome Trim & Arms**
Do NOT use any cleaners containing acids, ammonia or abrasives. The use of such products even in a diluted form may damage the finish.